

## DORMA RTS 88 OVERHEAD CONCEALED CLOSER

### TECHNICAL DETAILS

- HEADER - 1 3/4" x 4" ALUMINUM TUBE
- HANDING - DOUBLE ACTING
- PIVOTING - CENTRE LINE ONLY
- HOLD OPEN - SPECIFY: HOLD OPEN/ NO HOLD OPEN, 90°/105°
- DUTY - SPRING SIZE 3 (std): MEDIUM
  - 2 (opt): LIGHT
  - 4 (opt): HEAVY
- SPINDLE - 3/8" or 3/4" LONG
- DOOR WEIGHT - MAXIMUM 250 lbs (113 kg), DEPENDING on BOTTOM PIVOT
- DOOR SWING - 130° SWING ARC
- BACKCHECK - CUSHIONED STOP from APPROXIMATELY 85°.
  - IF ADJACENT STRUCTURES INTERFERE with MAXIMUM DEGREE of DOOR SWING, AUXILIARY DOOR STOP SHOULD BE INSTALLED.

EXTERIOR APPLICATION SURFACE APPLIED STOP REQUIRED.

