

## 520 SERIES TOP HUNG STRAIGHT SLIDER

\* AVAILABLE IN 4 TYPES OF TOP HUNG  
ROILING TRACK CONFIGURATIONS.

520-1 SERIES C-104 TRACK/C-106-4 NYLON ROLLERS - NOT TO EXCEED 85 Kg (175 lbs.)

Roller detail shown on Page 56

520-2 SERIES C-204 TRACK/C-995 ROLLERS - NOT TO EXCEED 182 Kg (400 lbs.)

Caster detail shown on Page 56

520-3 SERIES HSW SYSTEM - NOT TO EXCEED 150 Kg (330 lbs.)

Caster detail shown on Page 57

520-4 SERIES ST90 SYSTEM - NOT TO EXCEED 273 Kg (600 lbs.)

Caster detail shown on Page 57 (FOR MAINTENANCE REPAIRS ONLY)

### PANEL RAIL OPTIONS:

4" or 6" EXTRUDED ALUMINUM RAIL  
or VARIABLE HEIGHT COMPOSITE  
ALUMINUM RAIL (clad only)

### ALUMINUM FINISH:

See Page 02

### EXTRA FEATURES:

#### DOUBLE TRACK STYLE:

CYLINDER on OUTSIDE PANEL ONLY



THUMBTURN on INSIDE PANEL ONLY

#### INLINE TRACK STYLE:


CYLINDER on END PANELS

THUMBTURN on ALL PANELS WITH LOCKS

#331 PATCH can be INSTALLED INTO an INKAN  
RAIL. EXPOSED FASTENERS MAY be PRESENT.



AR1830 MODIFIED LOCK with  
CYLINDERS OUTSIDE - See Page 33



AR1830 MODIFIED LOCK with  
CYLINDERS OUTSIDE - See Page 33