

530 SERIES

TOP HUNG PARALLEL STAGGERED STACKING SLIDER


ADEQUATE STRUCTURAL SUPPORT REQUIRED.
Adequacy to be determined by project architect and/or structural engineer.

PANEL RAIL OPTIONS:


4" or 6" EXTRUDED ALUMINUM RAIL
or TOP PATCH SYSTEM (#331)
ALUMINUM RAIL (clad only)

* AVAILABLE IN 1 TYPE OF TOP HUNG ROLLING TRACK CONFIGURATIONS.

NOT TO EXCEED 150 Kg (330 lbs.)



AR1830 MODIFIED LOCK with CYLINDERS OUTSIDE - See Page 33



AR1830 MODIFIED LOCK with CYLINDERS OUTSIDE - See Page 33

STACKING ROOM with DOOR BY OTHERS

EXTRA FEATURES:
30" EGRESS DOOR (54" wide panel min.)
FLOOR GUIDE FIN OPTIONAL

