

## 540 SERIES

### TOP HUNG 90° STAGGERED STACKING SLIDER


ADEQUATE STRUCTURAL SUPPORT REQUIRED.  
Adequacy to be determined by project architect  
and/or structural engineer.

**PANEL RAIL OPTIONS:**


4" or 6" EXTRUDED ALUMINUM RAIL  
or TOP PATCH SYSTEM (#331)  
ALUMINUM RAIL (clad only)

\* AVAILABLE IN 1 TYPE OF TOP HUNG  
ROILING TRACK CONFIGURATIONS.


NOT TO EXCEED 150 Kg (330 lbs.)



AR1830 MODIFIED LOCK with  
CYLINDERS OUTSIDE - See Page 33



AR1830 MODIFIED LOCK with  
CYLINDERS OUTSIDE - See Page 33



STACKING ROOM with DOOR  
BY OTHERS

**EXTRA FEATURES:**

30" EGRESS DOOR (54" wide panel min.)  
FLOOR GUIDE PIN OPTIONAL