

NOT TO SCALE

NOM HEIGHT (A)
3' - 0"
3' - 6"
4' - 0"
5' - 0"
6' - 0"
7' - 0"
8' - 0"
CUSTOM HEIGHTS AVAILABLE


POST OPTION (C)
2" SQ X 14 GA
2 1/2" SQ X 12 OR 14 GA
3" SQ X 12 GA
4" SQ X 11 GA
6" SQ X 3/16" WALL

PICKET OPTION (D)	
3/4" SQ	14 GA
OR	16 GA
1" SQ	18 GA

A ____ " NOM HEIGHT
B ____ " NOM SECTION LENGTH
C ____ " POST SIZE ____ GAUGE
D ____ " PICKET SIZE ____ GAUGE
E ____ " POST LENGTH
F ____ " FACE TO FACE OF POSTS W/ STD. FLAT MOUNT BRACKET

**NOTES:**

- INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.
- DO NOT SCALE DRAWINGS.
- SPECIFICATIONS SHOWN CAN BE CHANGED ONLY BY THE MANUFACTURER..
- FOOTING WIDTH TO BE (4) X POST WIDTH.
- FENCE SECTIONS USING 3/4" PICKETS WILL TOTAL 19 PICKETS PER SECTION.  
 FENCE SECTIONS USING 1" PICKETS WILL TOTAL 18 PICKETS PER SECTION.
- CONTRACTORS NOTE: FOR PRODUCT AND COMPANY INFORMATION VISIT [www.CADdetails.com/info](http://www.CADdetails.com/info) REFERENCE NUMBER 2812-112.



**GUARDIAN PLUS FENCE**

2 RAIL