

NOM HEIGHT (A)
3'-0"
3'-6"
4'-0"
5'-0"
6'-0"
7'-0"
8'-0"
CUSTOM HEIGHTS AVAILABLE


POST OPTION (C)
2" SQ X 14 GA
2 1/2" SQ X 12 OR 14 GA
3" SQ X 12 GA
4" SQ X 11 GA
6" SQ X 3/16" WALL

PICKET OPTION (D)
3/4" SQ > 14 GA
OR > 16 GA
1" SQ > 18 GA

A ____ " NOM HEIGHT
B ____ " NOM SECTION LENGTH
C ____ " POST SIZE ____ GAUGE
D ____ " PICKET SIZE ____ GAUGE
E ____ " POST LENGTH
F ____ " FACE TO FACE OF POSTS W/ STD. FLAT MOUNT BRACKET

NOTES:

1. INSTALLATION TO BE COMPLETED IN ACCORDANCE WITH MANUFACTURERS SPECIFICATIONS.
2. DO NOT SCALE DRAWINGS.
3. SPECIFICATIONS SHOWN CAN BE CHANGED ONLY BY THE MANUFACTURER..
4. FOOTING WIDTH TO BE (4) X POST WIDTH.
5. FENCE SECTIONS USING 3/4" PICKETS WILL TOTAL 19 PICKETS PER SECTION.
FENCE SECTIONS USING 1" PICKETS WILL TOTAL 18 PICKETS PER SECTION.
6. CONTRACTORS NOTE: FOR PRODUCT AND COMPANY INFORMATION VISIT www.CADdetails.com/info
REFERENCE NUMBER 2812-160.



GUARDIAN PLUS GATE

3 RAIL, DOUBLE SWING GATE, 1 INCH PICKETS, 24 FT. OPENING (OR LARGER)