

NOTES:

- 1. REFER TO JOHNS MANVILLE WEBSITE (www.jm.com) FOR MOST UP-TO-DATE INFORMATION.
- 2. PLEASE SEE SINGLE PLY FLASHING SPECIFICATIONS FOR A FULL DESCRIPTION OF INSTALLATION INSTRUCTIONS AND REQUIREMENTS WHICH ARE CONSIDERED A PART OF THIS DETAIL.
- 3. ANY CARPENTRY OR METAL WORK SHOULD BE DESIGNED AND CONSTRUCTED IN ACCORDANCE WITH LOCAL CODE REQUIREMENTS AND/OR PROJECT SPECIFICATIONS. THESE COMPONENTS SHOULD BE REVIEWED AND APPROVED BY A LICENSED DESIGN PROFESSIONAL.
- 4. JM EPDM TAPE PRIMER OR JM SINGLE PLY MEMBRANE PRIMER (LOW VOC) MUST BE APPLIED ON ALL SURFACES COMING INTO CONTACT WITH JM EPDM SEAM TAPE. ROLL MEMBRANE WITH HAND ROLLER UNDER PRESSURE AT SEAM.
- 5. 1/8" TO 1/4" OF EPDM SEAM TAPE MUST BE EXPOSED.
- 6. MEMBRANE FASTENING REQUIRES RIGID COVER BOARD OVER JM INSULATION OR APPROVED WOOD NAILER SECURELY ANCHORED TO DECK WITHIN THIS ASSEMBLY.

EXPANSION JOINT ROOF TO ROOF WITH 6 INCH SEALING STRIP 30 YR

E-EJ-11
EXPANSION JOINT

	MEMBRANE TYPE:	ISSUE DATE
	JM EPDM	06-11-19
	MAXIMUM GUARANTEE TERM:	SCALE
	30 YEAR	N.T.S

Johns Manville is a manufacturer of commercial roofing products and offers this general conceptual information to you as a courtesy. This complimentary assistance is not to be used or relied upon by anyone as a substitute for professional engineering design and documentation required by building code, contract, or applicable law. By accepting these comments you agree they do not constitute any representations, endorsements of, or an assumption by Johns Manville of any liability for either the adequacy of the design of this building or any other material not supplied by Johns Manville.

