



Cat. No.	Type	Safe Working Load	A Length Open	B Length Closed	C Thread Size	D Eye ID	E Body Length	I Hook Opening	Weight Lb.	oz.
03-610	Eye/Hook	85 lbs.	8-3/4"	6-1/4"	10-32	5/16"	3-1/2"	1/4"		3
04-610	Eye/Hook	195 lbs.	10-1/4"	7-1/4"	1/4-28	3/8"	4-1/2"	3/8"		5
05-610	Eye/Hook	290 lbs.	11-1/2"	8-3/4"	5/16-24	1/2"	5-1/8"	1/2"		8
06-610	Eye/Hook	405 lbs.	13"	9"	3/8-24	5/8"	5-3/8"	5/8"		14
09-610	Eye/Hook	770 lbs.	15-1/2"	10-3/4"	1/2-20	3/4"	7"	3/4"	2	0
10-610	Eye/Hook	1,235 lbs.	18"	13"	5/8-18	7/8"	8-5/8"	7/8"	4	0

Note: Wireformed Hook & Welded Eye

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

Eye-to-Hook Stainless T-316 Tubular Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

EHSTTT-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/31/23



EAST HADDAM, CT 06423
TEL 1-800-874-7455
csjohnson.com