



Cat. No.	Type	Approx. Breaking strength	Safe Working Load	A Pin to Pin Length Open	B Pin to Pin Length Closed	C Thread Size	E Body Length	F Jaw Opening	G Jaw Throat	H Pin Dia.	Weight Lb.	oz.
03-110*	Jaw/Jaw	1000 lbs	400 lbs	6-3/8"	8-7/8"	10-32	3-1/2"	3/16"	3/4"	3/16"		2.5
04-100	Jaw/Jaw	2500 lbs	1000 lbs	8"	11"	1/4-28	4-1/2"	1/4"	3/4"	1/4"		5
04-110S*	Jaw/Jaw	2500 lbs	1000 lbs	6"	8"	1/4-28	3"	1/4"	1"	1/4"		4
04-110*	Jaw/Jaw	2500 lbs	1000 lbs	8"	11"	1/4-28	4-1/2"	1/4"	1"	1/4"		5
05-110*	Jaw/Jaw	4000 lbs	1600 lbs	9"	12-3/4"	5/16-24	5-1/8"	5/16"	1"	5/16"		8
06-110*	Jaw/Jaw	7000 lbs	2800 lbs	9-1/2"	13-3/4"	3/8-24	5-3/8"	3/8"	1-1/8"	3/8"		14
09-100-2	Jaw/Jaw	10,500 lbs	4200 lbs	12"	16-3/4"	1/2-20	7"	1/2"	1-1/16"	1/2"	1	12
10-100-2	Jaw/Jaw	14,800 lbs	5900 lbs	14"	19"	5/8-18	8-5/8"	5/8"	1-3/8"	5/8"	3	10

\* Jaws with "T" Toggle Construction. All others have Bronze Toggle Nuts.

JOHNSON ARCHITECTUAL REFERENCE DRAWING:

## Jaw-to-Jaw Stainless T-316 Tubular Turnbuckle

THIS DRAWING IS THE PROPERTY OF C. SHERMAN JOHNSON CO. INC. ANY REPRODUCTION OF THIS DOCUMENT WITHOUT THE EXPRESSED WRITTEN CONSENT OF C. SHERMAN JOHNSON CO. INC. IS STRICTLY PROHIBITED.

DRAWING No.

MATERIAL

MANUFACTURE

BY

DATE

JJSTTT-01

Type 316 Stainless Steel

C. Sherman Johnson Co., Inc.

SBG

7/31/23



**Johnson**  
Industrial Hardware

EAST HADDAM, CT 06423  
TEL 1-800-874-7455  
csjohnson.com