

E

D

C

B

A

NOTES:

RETRACTABLE CORD REEL, RTB SERIES:

CORD LENGTH: 25'

GAUGE: 12 AWG

CONDUCTOR: 3

MAX AMPS: 20 AMP

STANDARD: NEMA 2

CORD TYPE: SJOW-BLACK

VOLTS: 125 VAC

FEEDER END: 5-20P

PAYOUT END: YELLOW O/B 20A DUPLEX/DUPLEX

ALL STEEL CONSTRUCTION, INCLUDING MOUNTING BASE

SLIP RING RATED FOR 600 VOLTS/30 AMPS





12 POSITION ADJUSTABLE GUIDE ARM

ADJUSTABLE RATCHET CAN BE ENGAGED (POSITIVE LOCK) OR DISENGAGED (CONSTANT TENSION) AS NEEDED



ADJUSTABLE BALL STOP INCLUDED

6' FEEDER CORD INCLUDED

MADE IN USA



REVISIONS			
REV.	DESCRIPTION	DATE	NAME
-	UPDATED FORMAT	4/22/2020	

<div>PROPRIETARY AND CONFIDENTIAL</div> <div>This drawing and the information shown constitute trade secret and confidential property of KH Industries Inc. It is subject to recall, and is loaned for use only in connection with the authorized manufacture or installation of KH Industries Inc. products, and on the condition that it will be treated as confidential and will not be disclosed, published or reproduced in whole or in part, or permitted to be viewed or used by any other party, without specific written permission. Receipt and use of the drawing and information constitutes acceptance and agreement to the above.</div>	NAME		DATE		<div></div> <div>160 Elmview Ave. Hamburg, NY 14075 www.khindustries.com</div>		
	DRAWN		CWG			04/22/20	
	CHECKED		RG			04/22/20	
	APPROVED		RG			04/22/20	
	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES					SIZE: DRAWING NUMBER:	REV
	ANGULAR		.X	.XX	.XXX	B	-
± 1°		± .1	± .03	± .005	DESCRIPTION: RTB ASSEMBLY		
					Material	Finish	
THIRD ANGLE PROJECTION					-	-	
		SCALE: 1:4		DO NOT SCALE DRAWING		SHEET 1 OF 1	