






CAT-CT-24X24-016 - GFRG
SCALE 1/4
WGHT: 73.65 lbmass
AREA: 2015.45 in²
VOLUME: 1853.29 in³



4420 ANDREWS ST, STE A
NORTH LAS VEGAS, NV 89081
PH: (702) 968-0222
FAX: (702) 728-2777

ALL DRAWINGS MUST BE
SIGNED FOR APPROVAL
PRIOR TO PRODUCTION

☐ REVISE & RESUBMIT
☐ APPROVED AS NOTED
☐ APPROVED

X _____
DATE: _____

DELIVERY, STORAGE &
HANDLING

A. TRANSPORT, LIFT AND
HANDLE UNITS WITH CARE
AVOIDING EXCESSIVE STRESS
AND PREVENTING DAMAGE.
USE APPROPRIATE EQUIPMENT.

B. STORE PRODUCTS IN
MANUFACTURER'S UNOPENED
PACKAGING UNTIL READY FOR
INSTALLATION, IN A CLEAN DRY
AREA PROTECTED FROM
WEATHER, MOISTURE AND
DAMAGE. STORE UNITS
UPRIGHT AND NOT STACKED
UNLESS PERMITTED BY
MANUFACTURER.

TOLERANCES:
A. DIMENSIONAL OVERALL
TOLERANCE $\pm 1/4"$
B. THICKNESS $\pm 1/4"$
C. WARPAGE OR BOWING 1/16"
PER FOOT.

COMPANY NAME:

CUSTOMER

DESCRIPTION:

PROPERTY LOCATION

MATERIAL:
GFRG

PROJECT:
KEVIN O

DATE:
2/14/2024

REV:
1

PROJECT:
AREA OF WORK

SHEET:
15