


CAT-CT-24X24-017 - GFRG  
SCALE 1/4  
WGHT: 9.53 lbmass  
AREA: 2577.21 in<sup>2</sup>  
VOLUME: 239.84 in<sup>3</sup>



4420 ANDREWS ST, STE A  
NORTH LAS VEGAS, NV 89081

PH: (702) 968-0222  
FAX: (702) 728-2777

ALL DRAWINGS MUST BE  
SIGNED FOR APPROVAL  
PRIOR TO PRODUCTION

☐ REVISE & RESUBMIT  
☐ APPROVED AS NOTED  
☐ APPROVED

X \_\_\_\_\_

DATE: \_\_\_\_\_

#### DELIVERY, STORAGE & HANDLING

A. TRANSPORT, LIFT AND HANDLE UNITS WITH CARE AVOIDING EXCESSIVE STRESS AND PREVENTING DAMAGE. USE APPROPRIATE EQUIPMENT.

B. STORE PRODUCTS IN MANUFACTURER'S UNOPENED PACKAGING UNTIL READY FOR INSTALLATION, IN A CLEAN DRY AREA PROTECTED FROM WEATHER, MOISTURE AND DAMAGE. STORE UNITS UPRIGHT AND NOT STACKED UNLESS PERMITTED BY MANUFACTURER.

#### TOLERANCES:

A. DIMENSIONAL OVERALL TOLERANCE  $\pm 1/4"$

B. THICKNESS  $\pm 1/4"$

C. WARPAGE OR BOWING 1/16" PER FOOT.

#### COMPANY NAME:

CUSTOMER

#### DESCRIPTION:

PROPERTY LOCATION

#### MATERIAL:

GFRG

#### PROJECT:

KEVIN O

DATE:  
2/14/2024

REV:  
1

PROJECT:  
AREA OF WORK

SHEET:

17