



CAT-CT-24X24-019 - GFRG  
SCALE 1/4  
WGHT: 6.64 lbmass  
AREA: 1806.38 in<sup>2</sup>  
VOLUME: 167.21 in<sup>3</sup>



4420 ANDREWS ST, STE A  
NORTH LAS VEGAS, NV 89081  
PH: (702) 968-0222  
FAX: (702) 728-2777

ALL DRAWINGS MUST BE  
SIGNED FOR APPROVAL  
PRIOR TO PRODUCTION

☐ REVISE & RESUBMIT  
☐ APPROVED AS NOTED  
☐ APPROVED

X \_\_\_\_\_

DATE: \_\_\_\_\_

DELIVERY, STORAGE &  
HANDLING

A. TRANSPORT, LIFT AND  
HANDLE UNITS WITH CARE  
AVOIDING EXCESSIVE STRESS  
AND PREVENTING DAMAGE.  
USE APPROPRIATE EQUIPMENT.

B. STORE PRODUCTS IN  
MANUFACTURER'S UNOPENED  
PACKAGING UNTIL READY FOR  
INSTALLATION, IN A CLEAN DRY  
AREA PROTECTED FROM  
WEATHER, MOISTURE AND  
DAMAGE. STORE UNITS  
UPRIGHT AND NOT STACKED  
UNLESS PERMITTED BY  
MANUFACTURER.

TOLERANCES:

A. DIMENSIONAL OVERALL  
TOLERANCE  $\pm 1/4"$

B. THICKNESS  $\pm 1/4"$

C. WARPAGE OR BOWING 1/16"  
PER FOOT.

COMPANY NAME:

CUSTOMER

DESCRIPTION:

PROPERTY LOCATION

MATERIAL:

GFRG

PROJECT:

KEVIN O

DATE:  
2/14/2024

REV:  
1

PROJECT:  
AREA OF WORK

SHEET:

19