

Typical Gable Bracing



(1) 10d CC NAIL
TOE-NAIL FROM TOP.

TOP CHORD BRACE LOCATION

(3) 10d CC NAILS
TOE-NAIL TO TOP
CHORD AT BACK SIDE

JA-5 CLIP (046027)
@ ONE SIDE ONLY
W/1 1/4" X 10 GA
SHEAR NAILS:
(6) @ FLANGE INTO TRUSS
(3) @ FLANGE INTO BRACE

JA-5 ANGLE CLIP

INTERMEDIATE
RAFTER

GABLE
TRUSS

DIAGONAL GABLE END BRACE.
LOCATE AT COLUMN OR VERTICAL
STIFFENER.

ENDWALL
COLUMN

BOTTOM
CHORD

(4) 16d R.S.
NAILS (TYP.)
EA. MEMBER

BOTTOM CHORD BRACE LOCATION

DIAGONAL GABLE BRACE

(4) 16D R.S. NAILS
AT TRUSS TOP
CHORD

2-PLY STIFFENER
FASTEN WITH 2 ROWS
10d CC AT 24" O.C.
STAGGERED

24"

SEE FLOOR PLAN FOR
SIZE AND LOCATIONS
STIFFENER WILL EXTEND
TO HEADER OF DOOR
OPENINGS IF APPLICABLE.

(2) 16d GALV
R.S. NAILS @
EACH WEB

(4) 16D R.S. NAILS
AT TRUSS BOTTOM
CHORD


VERTICAL END WALL STIFFENER

TRUSS BTM.
CHORD

FALSE HEADER

(2) 10d CC
EACH MEMBER

OVERHEAD DOOR FALSE HEADER



PARTIAL HEIGHT SLIDING DOOR

TRUSS BTM.
CHORD

TRACK BACKER

(2) 10d CC
EACH MEMBER

(3) 10d CC
EACH MEMBER

