



MAPEI Products Assembly

1. Grout Options:

- | | | |
|----|------------------------------------|------------------|
| A. | <i>Ultracolor[®] Plus</i> | ISO 13007 CG2WAF |
| B. | <i>Keracolor™ U</i> | ISO 13007 CG2WA |
| C. | <i>Kerapoxy[®]</i> | ISO 13007 RG |
| D. | <i>Kerapoxy CQ</i> | ISO 13007 RG |
| E. | <i>MAPEI Flexcolor™ CQ</i> | |

2. Cementitious Bond Coat Options:

- | | | |
|----|---|---------------------|
| A. | <i>Kerabond/Keralastic™ System</i> | ISO 13007 C2E82P2 |
| B. | <i>Kerabond™ T / Keralastic™ System</i> | ISO 13007 C3E82P2 |
| C. | <i>Granrapid[®] System</i> | ISO 13007 C2F82P2 |
| D. | <i>Ultraflex™ 3</i> | ISO 13007 C2E8-1P1 |
| E. | <i>Ultraflex LFT™</i> | ISO 13007 C2TE8-1P1 |
| F. | <i>Ultraflex LFT Rapid</i> | ISO 13007 C2TF8-1P1 |

3. Bonded Waterproof Membrane Options:

- | | |
|----|--------------------------------|
| A. | <i>Mapelastic™ AquaDefense</i> |
| B. | <i>Mapelastic 315</i> |

4. Metal-Reinforced, Unbonded Mortar Bed:

- | | |
|----|----------------------------|
| A. | <i>Modified Mortar Bed</i> |
|----|----------------------------|