


# INTERIOR FLOORS OVER WOOD

Joists 16" (406 mm) o.c. / Plywood Subfloor  
Unbonded Mortar Bed  
Ceramic Tile

MAPEI: MF141  
TCNA: F141-16  
TTMAC: N/A  
Version: 2016



## MAPEI Products Assembly

### 1. Grout Options:

- |   |           |         |
|---|-----------|---------|
| A. <i>Ultracolor<sup>®</sup> Plus</i>         | ISO 13007 | C/G2WAF |
| B. <i>Keracolor<sup>™</sup> U</i>             | ISO 13007 | C/G2WA  |
| C. <i>Kerapoxy<sup>®</sup> or Kerapoxy CQ</i> | ISO 13007 | RG      |
| D. <i>MAPEI Flexcolor<sup>™</sup> CQ</i>      |           |         |

### 2. Cementitious Bond Coat Options:

- |  |           |          |
|--|-----------|----------|
| A. <i>Kerabond/Keralastic<sup>™</sup> System</i>                 | ISO 13007 | C2ES2P2  |
| B. <i>Kerabond<sup>™</sup> T / Keralastic<sup>™</sup> System</i> | ISO 13007 | C2ES2P2  |
| C. <i>Granraplo<sup>®</sup> System</i>                           | ISO 13007 | C2FS2P2  |
| D. <i>Ultraflex<sup>™</sup> LFT<sup>™</sup></i>                  | ISO 13007 | C2TES1P1 |
| E. <i>Ultraflex LFT Rapid</i>                                    | ISO 13007 | C2TFS1P1 |
| F. <i>Ultraflex 3</i>  | ISO 13007 | C2ES1P1  |

### 3. Optional Membrane Options:

- |                                      |  |
|--------------------------------------|--|
| A. (Waterproofing / Crack Isolation) | <i>Mapelastic<sup>™</sup> AquaDefense</i>  |
| B. (Waterproofing / Crack Isolation) | <i>Mapelastic 315</i>  |
| C. (Crack Isolation / Sound Control) | <i>Mapeguard<sup>™</sup> 2</i><br>– Requires <i>MAPEI S/M Primer<sup>™</sup></i> |
| D. (Crack Isolation)                 | <i>Mapelastic CI</i>   |

### 4. Unbonded Mortar Bed Options:

- |                               |
|-------------------------------|
| A. <i>Modified Mortar Bed</i> |
|-------------------------------|