


SCALE 1 : 4  
F1100-AS

STRAINER SIZE	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING			PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	
5"X3.65"X3.65" (127)X(93)X(93)	0.5"(13)	1.63"(41)	30 SQ IN	UPTO	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
				NB(-1) 2,000 LBS	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
				5,000 LBS TO	5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
				7,499 LBS	6"(152)	3.25"(83)	4.75"(121)	—	—	—

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
LINEAR : N/A  
ANGULAR : N/A  
UNLESS OTHERWISE SPECIFIED

P/N :

F1100-AS

SHEET : 1 OF 1

A5

REV :

0