


F1100-C-EF

SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX			PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	
5"(127)	1.56"(40)	2.69"(68)	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
			3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
			4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
			5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
			6"(152)	3.25"(83)	4.75"(121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-EF

SHEET : 1 OF 1

A5

REV :

0