


F1100-C-EG

SCALE 1 : 4

| STRAINER DIAMETER | STRAINER ADJUSTMENT |           | BODY HEIGHT |           |             |              |                  | PVC/ABS (-30/-31) |
|-------------------|---------------------|-----------|-------------|-----------|-------------|--------------|------------------|-------------------|
|                   | MIN                 | MAX       | PIPE SIZE   | NO HUB    | PUSH ON (P) | THREADED (T) | INSIDE CAULK (X) |                   |
| 5"(127)           | 1.56"(40)           | 2.69"(68) | 2"(51)      | 2.75"(70) | 3.375"(86)  | 2.25"(57)    | 3.75"(95)        | 2.94"(75)         |
|                   |                     |           | 3"(76)      | 2.75"(70) | 3.375"(86)  | 2.625"(67)   | 3.75"(95)        | 3.75"(95)         |
|                   |                     |           | 4"(102)     | 2.75"(70) | 3.375"(86)  | 2.625"(67)   | 3.75"(95)        | 3.75"(95)         |
|                   |                     |           | 5"(127)     | 2.75"(70) | —           | 2.625"(67)   | 3.75"(95)        | —                 |
|                   |                     |           | 6"(152)     | 3.25"(83) | 4.75"(121)  | —            | —                | —                 |

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
 LINEAR : N/A  
 ANGULAR : N/A  
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-EG

SHEET : 1 OF 1

A5

REV :

0