


F1100-C-FC

SCALE 1 : 4

TOP ASSEMBLY DIAMETER	TOP ASSEMBLY ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)	
	MIN	MAX	FREE AREA SQ IN	LOADRATING NB(-1) SS(-3)			PUSH IN(P)	THREADED (T)	INSIDE CAULK (X)		
7"(178)	1.125"(29)	1.88"(88)	12 SQ IN	UPTD 2,000 LBS	5000 TD 7499 LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
						3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
						4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
9"(229)	1.125"(29)	1.88"(88)	16.92SQ IN			5"(127)	3.25"(83)	—	2.625"(67)	3.75"(95)	—
						6"(152)	3.25"(83)	—	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :

LINEAR : N/A

ANGULAR : N/A

UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-FC

SHEET : 1 OF 1

A5

REV :

0