


F1100-C-K  
SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT MIN      MAX		ANSI/ASME RATING			BODY HEIGHT					
			FREE AREA SQ IN	LOAD RATING NB(-1)	RATING SS(-3)	PIPE SIZE	NO HUB	PUSH IN (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
5"(127)	1.56"(40)	2.69"(68)	15 SQ IN	UPTO 2,000 LBS	5000 TO 7499 LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
						3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
						4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
						5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
						6"(152)	3.25"(83)	4.75"(121)	—	—	—

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
LINEAR : N/A  
ANGULAR : N/A  
UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-K

SHEET : 1 OF 1

A5

REV :

0