


F1100-C-T  
SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA	LOAD RATING SS(-3)			PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	
6"(152)	1.75"(44)	2.69"(68)	9 SQ IN	5000 TD	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
					3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
7"(178)	1.63"(41)	2.75"(70)	12 SQ IN	7499 LBS	5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
					6"(152)	3.25"(83)	4.75"(121)	—	—	—

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4 in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :  
LINEAR : N/A  
ANGULAR : N/A  
UNLESS OTHERWISE SPECIFIED

P/N :

REV :

F1100-C-T

0