


F1100-C-VD
SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA	LOAD RATING SS(-3)			PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	
5"(127)	1.56"(40)	2.69"(68)	5 SQ IN	5000 TD 7499 LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
					3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
					6"(152)	3.25"(83)	4.75"(121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4 in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

REV :

F1100-C-VD

0