


F1100-C-ZS

SCALE 1 : 4

STRAINER SIZE SQUARE	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING						
6"(152)	1.94"(49)	2.75"(70)	12 SQ IN	NB(-1) UPTO 2.000 LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
				SS(-3) 5.000 LBS TO 7.499LBS	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
					6"(152)	3.25"(83)	4.75"(121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-ZS

SHEET : 1 OF 1

A5

REV :

0