


F1100-RS

SCALE 1 : 4

STRAINER SIZE	STRAINER ADJUSTMENT		ANSI/ASME RATING			PIPE SIZE	NO HUB	PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING							
4"(102) X 8"(203)	1.5"(38)	2.63"(67)	11 SQ IN	UPTO 2000 LBS	5000 TO 7499 LBS	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
4"(102) X 12"(305)	1.5"(38)	2.63"(67)	15 SQ IN	—	—	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
5"(127) X 17"(432)	1.5"(38)	2.63"(67)	20 SQ IN	—	—	4"(102)	2.75"(70)	—	2.625"(67)	3.75"(95)	3.75"(95)
						5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
						6"(152)	3.25"(83)	4.75"(121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-RS

SHEET : 1 OF 1

A5

REV :

0