


F1100-W(D)

SCALE 1 : 4

PIPE SIZE	NO HUB	BODY HEIGHT		INSIDE CAULK (X)	PVC/ABS (-30/-31)
		PUSH DN (P)	THREADED (T)		
2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
6"(152)	3.25"(83)	4.75"(121)	—	—	—

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
 LINEAR : N/A  
 ANGULAR : N/A  
 UNLESS OTHERWISE SPECIFIED

P/N :

F1100-W(D)

SHEET : 1 OF 1

A5

REV :

0