


F1100-C-HG
SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA SQ IN	LOAD RATING SS(-3)			PUSH IN (P)	THREADED (T)	INSIDE CAULK (X)	
5"(127)	1.56"(40)	2.69"(68)	8 SQ IN	5,000 LBS TO	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
7"(178)	1.69"(43)	2.81"(71)	12 SQ IN		7,499 LBS	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)
8"(203)	1.69"(43)	3.44"(87)	18 SQ IN	7,499 LBS	4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
					6"(152)	3.25"(83)	4.75"(121)	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :

LINEAR : N/A

ANGULAR : N/A

UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-HG

SHEET : 1 OF 1

A5

REV :

0