


F1100-C-RS

SCALE 1 : 4

STRAINER SIZE	STRAINER ADJUSTMENT		ANSI/ASME RATING			PIPE		BODY HEIGHT		THREADED	INSIDE	PVC/ABS
	MIN	MAX	FREE AREA SQ IN	LOADRATING NB(-1)SS(-3)	TO LBS	SIZE	NO HUB	PUSH DN (P)	(T)		CAULK (X)	
4" (102) X 8" (203)	2.56" (65)	3.81" (97)	11 SQ IN	UPTD 2000 LBS	5000 TO 7499 LBS	2" (51)	2.75" (70)	3.375" (86)	2.25" (57)	3.75" (95)	2.94" (75)	3.75" (95)
4" (102) X 12" (305)	2.56" (65)	3.81" (97)	15 SQ IN			3" (76)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)	
5" (127) X 17" (432)	2.56" (65)	3.81" (97)	20 SQ IN	—	—	4" (102)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)	—
						5" (127)	2.75" (70)	—	2.625" (67)	3.75" (95)	—	
						6" (152)	3.25" (83)	4.75" (121)	—	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-RS

REV :

0