


F1100-C-SHG

SCALE 1 : 4

STRAINER SIZE: SQUARE	STRAINER ADJUSTMENT		ANSI/ASME RATING		PIPE SIZE	NO HUB	BODY HEIGHT			PVC/ABS (-30/-31)
	MIN	MAX	FREE AREA	LOAD RATING SS(-3)			PUSH IN (P)	THREADED (T)	INSIDE CAULK (X)	
				5000	2"(51)	2.75"(70)	3.375"(86)	2.25"(57)	3.75"(95)	2.94"(75)
6"(152)	1.94"(49)	2.81"(71)	9SQ IN	TD	3"(76)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
					4"(102)	2.75"(70)	3.375"(86)	2.625"(67)	3.75"(95)	3.75"(95)
8"(203)	2.31"(59)	3.36"(86)	20SQ IN	7499	5"(127)	2.75"(70)	—	2.625"(67)	3.75"(95)	—
					6"(152)	3.25"(83)	4.75"(121)	—	—	—
				LBS						

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :

LINEAR : N/A

ANGULAR : N/A

UNLESS OTHERWISE SPECIFIED

P/N :

F1100-C-SHG

SHEET : 1 OF 1

A5

REV :

0