


F1140C

SCALE 1 : 5

MODEL NO	STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		CLEANOUT ASSEMBLY SIZE	CLEANOUT ASSEMBLY ADJUSTMENT		LOAD RATING		BODY HEIGHT	
		MIN	MAX	FREE AREA SQ IN	LOAD RATING		MIN	MAX	NB(-1)	DI(-4)	PIPE SIZE	NO HUB
F1140C-7	7" (178)	1.63" (41)	2.63" (67)	11 SQ IN	NB(-1) SPECIAL DUTY OVER	5" (127)	1.63" (41)	2.63" (67)	UPTO 2,000 LBS	5K TO 7,499 LBS	2" (51)	13.5" (345)
F1140C-9	9" (229)	1.88" (48)	2.63" (67)	18 SQ IN	DI(-4) 10000 LBS						3" (76)	
											4" (102)	

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 5

in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

F1140C

REV :

0