


F1160
SCALE 1 : 4

STRAINER DIAMETER	STRAINER ADJUSTMENT		ANSI/ASME RATING		BODY HEIGHT		
	MIN	MAX	FREE AREA SQ IN	LOAD RATING NBC(-1)	PIPE SIZE	NO HUB	CENTER OF OUTLET TO TOP OF BODY
4"(102)	0.5"(13)	1.5"(38)	3.5 SQ IN	UPTD 2,000 LBS	2"(51)	7.875"(200)	3.75"(95)
					3"(76)	7.875"(200)	3.75"(95)

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4 in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

REV :

F1160

0