


F1170-C-SD
SCALE 1 : 4

STRAINER SIZE	STRAINER ADJUSTMENT		ANSI/ASME RATING		BODY HEIGHT		
	MIN	MAX	FREE AREA SQ IN	LOAD RATING	PIPE SIZE NO HUB	A	B
5" (127) X 5" (127)	3.06" (78)	4.31" (110)	12 SQ IN	SS(-3) 5,000 LBS TD 7,499 LBS	2" (51) 3" (76)	3.75" (95)	7.875" (200)

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4 in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

REV :

F1170-C-SD

0