


F1550  
SCALE 1 : 4

TOP ASSEMBLY DIAMETER	ANSI/ASME		BODY HEIGHT					
	FREE AREA	LOAD RATING NB(-1)SS(-3)DI(-4)	PIPE SIZE	NO HUB (STANDARD)	PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (30/31)
15"(381)	60 SQ IN	"SPECIAL DUTY" (OVER 10 000 LBS)	2"(51)	5.437(138)	6.125"(156)	5.437(138)	6.25(158)	7.125"(181)
			3"(76)	5.437(138)	6.125"(156)	5.437(138)	6.25(158)	8.125"(206)
			4"(102)	5.437(138)	6.125"(156)	5.437(138)	6.25(158)	8.125"(206)
			5"(127)	5.437(138)	—	5.437(138)	6.25(158)	—
			6"(152)	5.875(149)	8"(203)	6"(152)	6.25(158)	—
			8"(203)	5.875(149)	—	—	—	—

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
LINEAR : N/A  
ANGULAR : N/A  
UNLESS OTHERWISE SPECIFIED

P/N :

F1550

SHEET : 1 OF 1

A5

REV :

1