


R1100-RS  
SCALE 1 : 4

ANSI/ASME RATING	BODY HEIGHT					
FREE AREA SQ IN	PIPE SIZE	NO HUB	PUSH DN (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
15 SQ IN	2" (51)	2.75" (70)	3.375" (86)	2.25" (57)	3.75" (95)	2.94" (75)
	3" (76)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)
	4" (102)	2.75" (70)	3.375" (86)	2.625" (67)	3.75" (95)	3.75" (95)
	5" (127)	2.75" (70)	—	2.625" (67)	3.75" (95)	—
	6" (152)	3.25" (83)	4.75" (121)	—	—	—

**MIFAB**

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :  
LINEAR : N/A  
ANGULAR : N/A  
UNLESS OTHERWISE SPECIFIED

P/N :

R1100-RS

SHEET : 1 OF 1

A5

REV :

0