


R1200-RS

SCALE 1 : 4

ANSI/ASME DOME FREE AREA	BODY HEIGHT					
	PIPE SIZE	NO HUB (STANDARD)	PUSH ON (P)	THREADED (T)	INSIDE CAULK (X)	PVC/ABS (-30/-31)
35 SQ IN	2"(51)	5.437(138)	6.125"(156)	5.437(138)	6.25(159)	7.125"(181)
	3"(76)	5.437(138)	6.125"(156)	5.437(138)	6.25(159)	8.125"(206)
	4"(102)	5.437(138)	6.125"(156)	5.437(138)	6.25(159)	8.125"(206)
	5"(127)	5.437(138)	—	5.437(138)	6.25(159)	—
	6"(152)	5.875(149)	8"(203)	6"(152)	6.25(159)	—
	8"(203)	5.875(149)	—	—	—	—

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

GENERAL TOLERANCE :
 LINEAR : N/A
 ANGULAR : N/A
 UNLESS OTHERWISE SPECIFIED

P/N :

R1200-RS

SHEET : 1 OF 1

A5

REV :

0