



C1450-R

SCALE 1 : 4

PIPE SIZE (NO HUB)	NICKEL BRONZE COVER DIAMETER	CLEANOUT PLUG COVER SIZE	BODY HEIGHT		
			PIPE SIZE	NO HUB	PVC/ABS (-30/-31)
2"(51)	ø 6"(152)	ø 5.06"(129)	2"(51)	2.5"(64)	2.94"(75)
3"(76)			3"(76)	2.5"(64)	2.94"(75)
4"(102)			4"(102)	2.5"(64)	2.94"(75)

MIFAB

FOR CATALOGUE USE ONLY

	SCALE : 1 : 4	in/[mm]	GENERAL TOLERANCE : LINEAR : N/A ANGULAR : N/A UNLESS OTHERWISE SPECIFIED	P/N :	C1450-R
	SHEET : 1 OF 1	A5		REV :	0