


C1460-R

SCALE 1 : 4

PIPE SIZE (NO HUB)	BODY HEIGHT	NICKEL BRONZE COVER DIAMETER
2"(51)	6.5"(165)	6"(152)
3"(76)	8.125"(206)	6"(152)
4"(102)	9.75"(248)	6"(152)
6"(152)	14"(356)	9"(229)
8"(204)	17"(432)	9"(229)

MIFAB

FOR CATALOGUE USE ONLY



SCALE : 1 : 4

in/[mm]

SHEET : 1 OF 1

A5

GENERAL TOLERANCE :
LINEAR : N/A
ANGULAR : N/A
UNLESS OTHERWISE SPECIFIED

P/N :

C1460-R

REV :

0