



Notes: 1. Rack Marks NOT Allowable

Rev	Date	Int.	Description
.	.	.	.



Exposed Surfaces
Scale 1 : 1

A54-0154

Units Of Tolerance : IN

Angular:	± 1°
Fractional:	± 1/64
Decimal:	
0.000 - 0.124 ±	0.007
0.125 - 0.249 ±	0.008
0.250 - 0.499 ±	0.009
0.500 - 0.749 ±	0.010
0.750 - 0.999 ±	0.012
1.000 - 1.499 ±	0.014
1.500 - 1.999 ±	0.015
2.000 - 3.999 ±	0.025
4.000 - 6.000 ±	0.035
> 6.000 ±	0.050

Unspecified:	PROPRIETARY & CONFIDENTIAL:
Radius: 0.000	THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MORSE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MORSE INDUSTRIES IS PROHIBITED. ALL RIGHTS RESERVED.
Wall: 0.000	
Scale: 4 : 1	
Plot Size: A	
Sheet: 1 of 1	

PROPRIETARY & CONFIDENTIAL:
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF MORSE INDUSTRIES. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF MORSE INDUSTRIES IS PROHIBITED. ALL RIGHTS RESERVED.

Title: Extruded Double Channel Slide Track	
Material: Aluminum	Grade: 6463
Finishes: Satin Anodize (VEL); Bright Chrome (BLY); Bright Gold (BLG)	
Cut Lengths: (144") 12.000' ± .000"	(000") 00.000' ± .000"
Per. 5.3999 in	Total Per. 5.3999 in
Area: 0.1496 in ²	Weight: 0.1777 lb/ft

Fits To:
Temper: T-5
Engineer: G.J. Worthy
Date: 06/10/2005

MORSE INDUSTRIES
Working Solutions in Aluminum, Plastics and Stainless Steel

Telephone: (800) 325-7513
Fax: (800) 411-8226
www.morseindustries.com