


4

3







2

1

ClimaCLEAR Concept 1



<< unlimited number of panels >>



|                                      |  |  |      |   |  |  |
|--------------------------------------|--|--|------|---|--|--|
| UNLESS OTHERWISE SPECIFIED:          |  | NAME   | DATE | TITLE: <div><div>NanaWall<sup>®</sup></div><div>Engineering the Exceptional</div></div> |  |  |
| DIMENSIONS ARE IN INCHES             |  | DRAWN  |      |   |  |  |
| TOLERANCES:                          |  | CHECKED  |      |   |  |  |
| FRACTIONAL ±                         |  | ENG APPR.  |      |   |  |  |
| ANGULAR: MACH ± BEND ±               |  | MFG APPR.  |      | Q.A.  |  |  |
| TWO PLACE DECIMAL ±                  |  |  |      |   |  |  |
| THREE PLACE DECIMAL ±                |  |  |      |   |  |  |
| INTERPRET GEOMETRIC TOLERANCING PER: |  | PROPRIETARY AND CONFIDENTIAL   |      | SIZE DWG. NO. REV   |  |  |
| MATERIAL                             |  | THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF NANA WALL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF NANA WALL IS PROHIBITED. |      |   |  |  |
| FINISH                               |  |  |      |   |  |  |
| DO NOT SCALE DRAWING                 |  |  |      |   |  |  |

4

3

2

1

D

D

C

C

B

B

A

A