














HSW75 Concept D



<< unlimited number of panels >>



UNLESS OTHERWISE SPECIFIED:		NAME	DATE	TITLE: NanaWall Engineering the Exceptional	
DIMENSIONS ARE IN INCHES	DRAWN				
TOLERANCES:	CHECKED				
FRACTIONAL: ±	ENG APPR.				
ANGULAR: MACH ± BEND ±	MFG APPR.			SIZE DWG. NO. REV	
TWO PLACE DECIMAL ±	Q.A.			SCALE: 1:40 (1:4) SHEET 1 OF 1	
THREE PLACE DECIMAL ±					
INTERPRET GEOMETRIC TOLERANCING PER:					
MATERIAL	PROPRIETARY AND CONFIDENTIAL THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF NANA WALL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF NANA WALL IS PROHIBITED.				
FINISH					
DO NOT SCALE DRAWING					