









HSW75 Concept O



<< unlimited number of panels >>



| | | | | | |
|--------------------------------------|--|--|------|--|-------------------|
| UNLESS OTHERWISE SPECIFIED: | | NAME | DATE | TITLE: <div>NanaWall® Engineering the Exceptional</div> | |
| DIMENSIONS ARE IN INCHES | | DRAWN | | | |
| TOLERANCES: | | CHECKED | | | |
| FRACTIONAL: ± | | ENG APPR. | | | |
| ANGULAR: MACH ± | | MFG APPR. | | Q.A. | SIZE DWG. NO. REV |
| BEND ± | | | | | |
| TWO PLACE DECIMAL ± | | | | | |
| THREE PLACE DECIMAL ± | | | | | |
| INTERPRET GEOMETRIC TOLERANCING PER: | | | | | |
| MATERIAL | | PROPRIETARY AND CONFIDENTIAL | | | |
| FINISH | | THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF NANA WALL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF NANA WALL IS PROHIBITED. | | | |
| DO NOT SCALE DRAWING | | | | SCALE: 1:40 (1:4) | |