




1 ELEVATION - POSITION

3 QUANTITY [1]

(TYPICAL: ELEVATIONS SHOWN FROM INTERIOR)

NANA WALL NW WOOD 540

CONFIGURATION: OUTWARD 6 LEFT - OUTWARD 3 RIGHT

SILL TYPE: FLUSH SILL THERMALLY BROKEN

MOUNT OPTION: FLOOR


* FIRST PANEL OPEN

NOTE:

FOR SUGGESTED ROUGH OPENING DIMENSION PLEASE SEE FRAME SECTION DETAILS ON FOLLOWING DETAIL SHEET


THESE DRAWINGS ARE BASED ON A UNIT HEIGHT OF 8' AND UNIT WIDTH IN INCREMENTS OF 3' FOR EACH PANEL. THE PURPOSE IS ONLY TO SHOW RELEVANT CROSS SECTION DETAILS AND VARIOUS DIMENSIONS APPLICABLE ONLY FOR THIS SPECIFIC UNIT SIZE. IF DRAWINGS FOR OTHER UNIT SIZES ARE DESIRED, PLEASE CONTACT NANAWALL.

PLEASE SEE DETAILS TAB FOR CROSS SECTIONS OF HEAD, SILL AND SIDE WALLS.



PANELS CLOSED

FINISH FLOOR LEVEL WITHIN DASHED LINE NOT TO EXCEED THE FINISH FLOOR LEVEL AT NANAWALL SILL



PANELS OPEN

A PLAN SECTION (POSITION)

3 1/2"=1'

