




1 ELEVATION - POSITION

3 QUANTITY [1]

(TYPICAL: ELEVATIONS SHOWN FROM INTERIOR)

NANA WALL NW ACOUSTICAL 645


CONFIGURATION: OUTWARD 2 LEFT - OUTWARD 2 RIGHT

SILL TYPE: FLUSH SILL THERMALLY BROKEN


MOUNT OPTION: FLOOR

\* FIRST PANEL OPEN

NOTE:  
FOR SUGGESTED ROUGH OPENING DIMENSION  
PLEASE SEE FRAME SECTION DETAILS ON FOLLOWING  
DETAIL SHEET  
THESE DRAWINGS ARE BASED ON A UNIT HEIGHT OF  
8' AND UNIT WIDTH IN INCREMENTS OF 3' FOR  
EACH PANEL. THE PURPOSE IS ONLY TO SHOW  
RELEVANT CROSS SECTION DETAILS AND VARIOUS  
DIMENSIONS APPLICABLE ONLY FOR THIS SPECIFIC  
UNIT SIZE. IF DRAWINGS FOR OTHER UNIT SIZES  
ARE DESIRED, PLEASE CONTACT NANAWALL.  
PLEASE SEE DETAILS TAB FOR CROSS SECTIONS OF  
HEAD, SILL AND SIDE JAMB




PANELS CLOSED




A PLAN SECTION (POSITION )


4 1/2"=1'



**A** VERTICAL SECTION  
NW ACOUSTICAL 645



**4** FOLDING WITH HANDLE  
NW ACOUSTICAL 645



**5** FOLDING PANEL MEET FOLDING PANEL  
NW ACOUSTICAL 645