


REV	ECD	DESCRIPTION	DATE	INL	INL
H	12694	3FT BULB UPDATE	06/04/2015	JK	DSH



PLACE TAG DRY CONTACTS TO THESE WIRES

POWER SPECIFICATIONS
115 VAC 60 Hz SINGLE PHASE

- OUTLETS NOT TO EXCEED 3 AMPS.
- INDICATES WIRE NUMBER
- INDICATES ITEM NUMBER
- - - INDICATES OPTIONAL WIRING
- * INDICATES BRAKE IN WIRING WHEN OPTION IS USED
- (FOLLOW DASHED WIRING)

NOTE 1: OPTIONAL WIRING USED FOR HINGED WINDOW



NU-543-300/400/500/600	115 VAC, 60 HZ (ENERGY SAVER ECM MOTOR)
DFTMLS 10/15/13 CHKD BP	ELECTRICAL SCHEMATIC
DRAWING NUMBER	BCD-16378 H
	SHEET 1 OF 2