

1.00 min 0.988 not to exceed 1.035

Width  $-.063$  to  $+.125$

A

B

IG's between  
42" & 76.750"  
Edge of Glass  
to Top of Track  
 $7.51 \pm 0.31$

IG's between  
76.8125" & 80"  
Edge of Glass  
to Top of Track  
 $5.76 \pm 0.31$

Edge of Glass to  
Edge of Operator  
 $2.031 \pm .031$

Length  
 $-.063$  to  $+.125$

C

Edge of Glass to  
Edge of Track  
 $.655 \pm .031$

D