



TRACPIPE COUNTERSTRIKE: NOMINAL DIMENSIONS			
PART NUMBER	JACKET OD	CSST OD	CSST ID
FGP-CS-375	0.690	0.600	0.441
FGP-CS-500	0.865	0.788	0.599
FGP-CS-750	1.125	1.030	0.820
FGP-CS-1000	1.395	1.315	1.060
FGP-CS-1250	1.688	1.600	1.290
FGP-CS-1500	1.923	1.840	1.525
FGP-CS-2000	2.485	2.415	2.060

<p align="center">NOTICE - PROPRIETARY INFORMATION</p> <p>This drawing is the property of OmegaFlex, Inc. and must be returned without reproduction or duplication, at any time upon request but in any event as soon as it has served the purposes for which it is furnished. While in possession of the recipient, it must be properly safeguarded against disclosure to anyone except those employees who require it for work or job. The recipient must keep confidential and required his (its) employees to keep the information contained hereon.</p>			
<p>TOLERANCES</p>		<p align="center">OmegaFlex Manufacturer of Flexible Metal Hose and Gas Piping Products 451 Creamery Way, Exton, PA 19341-2509</p>	
<p>TITLE FGP-CS-XXX</p>		<p>REV NC</p>	
<p>DRAWN K. KEALEY</p>	<p>5/6/2025</p>	<p>SIZE C</p>	<p>AUTODESK INVENTOR</p>
<p>APRD B. BREITINGER</p>		<p>DWG NO FGP-CS-XXX</p>	
<p>MATERIAL</p>		<p>SCALE See Drawing</p>	<p>SHEET 1 OF 1</p>
<p>MODEL FILE: K:\CAD\FGP FITTINGS\BIM MODEL CONVERSIONS\FGP-CS-XXX\MOC FGP-CS-XXX.iam</p>			
<p>DRAWING FILE: K:\CAD\FGP FITTINGS\BIM MODEL CONVERSIONS\FGP-CS-XXX\CounterStrike Pipe.idw</p>			