


ML-758

DRYER NOTES:


- * DUCTWORK SIZE VARIES WITH INSTALLATION CONDITIONS.
- * EXHAUST STATIC PRESSURE MUST BE NO LESS THAN 0 AND MUST NOT EXCEED 0.7" (1.74 MB) WATER COLUMN.

STEAM DRYER NOTES:


- * OPERATING HEIGHT OF STEAM DRYER IS 79" (200.6 CM).
- * SIZE OF PIPING TO DRYER VARIES WITH INSTALLATION CONDITIONS. CONTACT FACTORY FOR ASSISTANCE.
- * STANDARD STEAM DRYERS MUST BE PROVIDED WITH CLEAN, DRY, REGULATED 80 PSI \pm 10 PSI (5.5 BAR \pm 0.69 BAR) AIR SUPPLY.



PLAN VIEW



REAR VIEW (GAS AND ELECTRIC)



FRONT VIEW

REAR VIEW (STEAM ONLY)