


Motorized Retractable Wall Screen

Recessed Roller Placement Details -


Minimum Cavity Size for 4" Roller




**PLACEMENT OF 4" ROLLER,
5-1/2" ROLLER MOUNTING BRACKET
AND RECESSED SIDE TRACK**

PRODUCT LIMITATION

**SIZE LIMITATION FOR THE 4 INCH ROLLER IS:
20 FEET (Wide) x 11 FEET (High/Pull Length)**



**RELATIONSHIP OF U-CHANNEL
TO MOTOR BRACKET IN A MINIMUM
RECESSED CAVITY C/W 4" ROLLER**



**RELATIONSHIP OF THE
SIDE TRACK U-CHANNEL
TO THE 5-1/2" MOTOR MOUNTING BRACKET**

All dimensions are given in inches, millimeters conversion in brackets

NOTE:

Smaller cavity sizes may be available for your application; Please check with your local Phantom Authorized Distributor.

Rev #	Description of Revision	Approved by	Rev Date
Rev 03	Title change	N.D.R.	03/06/18
Rev 02	Modify the relationship between the U-Channel and the Motor Bracket in a cavity	N.D.R.	01/28/16
Rev 01	Addition of Track Entry Guides on Recessed Track	N.D.R.	01/16/16

Rev #	Description of Revision	Approved by	Rev Date
Creator:	Date:	Approved By/Date:	
N.D.R.	07/15/2015		
Drawing Title:			
PSEXECINSTALLMINCAVITYSIZE4INCH02			Scale:
© 2016 Phantom Mfg. Intl Ltd.			1 : 1