


INDUSTRIAL STAIRWAY & PLATFORM

(A) BAR GRATING TREAD
(GROOVED NOSING)



TREAD WELDED AND BOLTED TO STRINGER WITH 3/8" HEX HEAD BOLTS

1-1/4" SCH 40 ALUMINUM PIPE HANDRAIL/GUARDRAIL (6005-T5)

NOTE:
ALL BOLTS/FASTENERS NECESSARY TO ANCHOR STAIRWAY ARE BY OTHERS.

30" MIN.

BAR GRATING
TOE BOARDS

1/4" MOUNTING PLATE (DIMENSIONS VARY)

8" x 2-1/4" x 1/4" ALUMINUM CHANNEL (TYPICAL)

UNIFORM RISER HEIGHTS AND TREAD DEPTHS BETWEEN LANDINGS

6-1/2" MIN.
9-1/2" MAX.

9-1/2" MIN.

30°-45° (AVAILABLE RANGE)

4" FLAT BAR FOR MOUNTING

AS REQ'D

2 1/4"

22" MIN.

3'-6"

VERTICAL HEIGHT

MAX 15'

CLEAR TREAD
29-1/2" MIN
55-1/2" MAX

CLEAR TREAD + 4-1/2"

FACTORY FINISH
ALUMINUM-MILL FINISH

PS-4

OSHA 1910.25 & 29

Precision Ladders, LLC
P.O. BOX 2279 Morristown, TN 37816-2279
Ph: (423) 586-2265 Fax: (423) 586-2091
www.PrecisionLadders.com

DWG. CHECK	ARCH'T OR ENG'R.	PROJECT		PRECISION REP
BUILT BY:	PURCHASE ORDER	WORK ORDER	PURCHASER	SERIAL#
CHECKED BY:	DRAWN BY: DNH	DATE: 4/8/19	MODEL# PS-	QTY.