


# DELMAR SERIES. ADJUSTABLE LENGTH LINEAR DRAIN WEDGEWIRE. 3" HIGH FLOW OUTLET. 2D SET


Note:

- For indoor and outdoor use.
- Modify length of grate and channel on-site to exact specifications.
  - Place outlet anywhere along channel run.
- Select the drain equal to or longer than final desired length.
- For lengths longer than 96", connect multiple drains to build desired length.
- Corner accessory available when connecting two drains in a 90 degree angle.



36" MIST, ONE OUTLET



48" MIST, ONE OUTLET




60" MIST, ONE OUTLET



For spec., installation instructions, installation videos, pictures and more information visit:  
<https://qmdrain.com/product/wedgewire-adjustable-delmar-linear-drain/>

72" MIST, TWO OUTLETS




Full length drain can be built using either one or both included outlets.



Corner.  
 Needed when  
 connecting two  
 bases in a 90  
 degree angle.

96" MIST, TWO OUTLETS



Full length drain can be built using either one or both included outlets.